

Rittal – The System.

Faster – better – everywhere.



AS 4052.131 Screwdrivers

State: 11/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4052.131 - Screwdrivers insulated

With a long, slender handle and high-performance tip with non-transfer insulation.

Features

Model No.	AS 4052.131
Design	Isolation protection 1000 V for Phillips-head screws
Product description	With a long, slender handle and high-performance tip with non-transfer insulation.
Benefits	Minimal force required, thanks to ergonomically styled handle Handle head with anti-roll protection and clear screw labelling Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than comparable tools Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working
Material	Blade: Chrome-molybdenum-vanadium alloy Handle core: Hard plastic Handle body: Elastic, highly flexible plastic
Colour	Handle: Anthracite and Rittal Power Pink
Blade dia.	4.5 mm
Blade length	80 mm
Blade tip	PH 1
Handle dia.	25 mm
Handle length	105 mm
Standards	IEC 60 900
Packs of	3 pc(s).
Customs tariff number	82054000
ETIM 9	EC000144
ETIM 8	EC000144

Features

ECLASS 8.0

21040406

Product description

Screwdriver insulated PH