

Rittal – The System.

Faster – better – everywhere.



AS 4054.141 Crimping pliers

State: 02/03/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.141 - Crimping pliers for ring terminals

For use with insulated ring terminals and connectors

Features

| | |
|-----------------------|---|
| Model No. | AS 4054.141 |
| Design | Straight |
| Product description | For use with insulated ring terminals and connectors. |
| Benefits | Clear allocation of cross-sections, thanks to colour coding on the dies Releasable ratchet Releases as soon as the required pressure is reached, to prevent underpressing |
| Material | High-quality special tool steel |
| Surface finish | Matt, plated |
| Colour | Handle: Anthracite and Rittal Power Pink |
| Compression | Oval crimp |
| Dimensions | Height: 68 mm Length: 256 mm |
| AWG | 22 - 10 |
| For cross-section | 0.75 - 6 mm ² |
| Packs of | 1 pc(s). |
| Net weight | 0.64 kg |
| Gross weight | 0.68 kg |
| Customs tariff number | 82032000 |
| ETIM 9 | EC000168 |
| ETIM 8 | EC000168 |
| ECLASS 8.0 | 21043811 |
| Product description | Crimping plier 0.5 - 6 mm ² , Oval-Cr. |