

Rittal – The System.

Faster – better – everywhere.



AS 4055.115

Splitter hole punch, round

State: 25/08/2025 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.115 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.115 |
| Design | With triple splitting |
| Product description | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes | Female dies Male dies |
| Machinable material | Stainless steel |
| Maximum machinable material thickness, stainless steel | 2 mm |
| Ø punch | 15.2 mm |
| Note | When operating with wrenches, tension screws with ball bearings should be used. |
| Suitable for hydraulic bolt order number | 4055.665 |
| Tension screw (Ø x L) | 11.1 x 60 mm |
| Hydraulic tension screw Ø | 11.1 mm 19 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.039 |
| Gross weight | 0.054 |
| Customs tariff number | 82073010 |
| EAN | 4028177807976 |
| ETIM 9 | EC000156 |

Features

| | |
|------------|----------|
| ETIM 8 | EC000156 |
| ECLASS 8.0 | 21049047 |