

# Rittal – The System.

Faster – better – everywhere.



## TS 4579.000 Support strip

State: 22/05/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 4579.000 - Support strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



## Features

Model No.	TS 4579.000
Product description	For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.
Technical specifications	4.5 mm diameter hole on a 25 mm pitch pattern
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Length	790 mm
To fit door width	900 mm
VX SE installation options	In door width 900 mm In enclosure width 800 mm, on the inner mounting level
AX installation options	In enclosure width 800 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
AX stainless steel installation options	In enclosure width 800 mm In door width 800 mm, in conjunction with the perforated door strip
TS installation options	In enclosure width/depth 800 mm, on the inner mounting level

# Features

---

TP installation options	In TP pedestal and one-piece console pedestal width 800 mm, in conjunction with rail for interior installation for TP, compact enclosure HD
To fit	Enclosure type: TS VX SE TP AX Width/depth: 800 mm
Packs of	20 pc(s).
Net weight	8 kg
Gross weight	8.1 kg
PCF per pack (cradle-to-gate)	37.23 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	TS Support strip, for TS, VX SE, TP, for inner mounting level: for W/D: 800 mm, for door width: 900 mm, L: 790 mm

---

# Approvals

---

Explanations	PCF-declaration
--------------	-----------------