

Rittal – The System.

Faster – better – everywhere.



VX 5301.348

Gland plate module for side cable entry

State: 23/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.348 - Gland plate module for side cable entry for VX IT

With adjustable openings and brush strips on both sides. The version which is open at the side even allows retrospective fitting of the base plate module with the cables already installed.

Features

| | |
|-------------------------------|---|
| Model No. | VX 5301.348 |
| Product description | With adjustable opening and brush strips on both sides. The version which is open at the side even allows the base plate module to be retro-fitted with the cables already installed. |
| Material | Module plate: Sheet steel Brush strip: Plastic, UL 94 HB, halogen-free |
| Surface finish | Module plate: Zinc-plated |
| Supply includes | Assembly parts |
| Assembly instruction | Several gland module plates must be combined to seal the base completely in the VX IT The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm. |
| Note | Gland plate modules with brush strip not suitable for applications with a protection category to IEC 60 529 |
| To fit | Enclosure type: VX IT Width: = 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 2 kg |
| Gross weight | 2.36 kg |
| PCF per pack (cradle-to-gate) | 9 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |

Features

ECLASS 8.0

27189261

Product description

Gland plate module for cable entry, for VX IT, adjustable opening and brush strips on each side, for enclosure width 800 mm, module: sheet steel, zinc-plated