

# Rittal – The System.

Faster – better – everywhere.



## VX 5302.164 Depth stays

State: 24/08/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5302.164 - Depth stays for 482.6 mm (19") mounting angles

L-shaped mounting angles, also for accommodating server system installation kits.

## Features

|                      |  |
|----------------------|--|
| Model No.            | VX 5302.164  |
| Design               | for VX IT 482.6 mm (19") mounting angles, dynamic  |
| Product description  | To accommodate 19" mounting angles.  |
| Benefits             | Particularly high load capacity up to 15,000 N<br>Enhanced stability thanks to improved load distribution<br>Symmetrical or asymmetrical installation supported<br>More space for cable routing or integration of a Liquid Cooling Unit (LCU) with one-sided, asymmetrical (laterally offset) installation<br>Ideal for integrating 482.6 mm (19") mounting angles for alternative installation with 21", 23", or 24" components |
| Material             | Sheet steel  |
| Surface finish       | Spray-finished   |
| Colour               | RAL 9005   |
| Supply includes      | Depth stays<br>Assembly parts<br>4 support strips (2 top, 2 bottom)  |
| Assembly instruction | For the attachment of mounting angles in enclosures that are greater than 1000 mm deep and greater than 600 mm wide, an additional support rail for VX IT is required  |
| To fit               | Enclosure type: VX IT, dynamic<br>Width: > 600 mm<br>Depth: = 1,200 mm   |
| Packs of             | 4 pc(s).   |
| Net weight           | 12   |
| Gross weight         | 12.5   |

# Features

|                               |  |
|-------------------------------|--|
| PCF per pack (cradle-to-gate) | 47.6 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 73269098   |
| EAN                           | 4028177955592  |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |

# Approvals

|              |                            |
|--------------|----------------------------|
| Explanations | Manufacturer's declaration |
|--------------|----------------------------|