

Rittal – The System.

Faster – better – everywhere.



DK 5501.440

Slide rail, 1 U, static installation

State: 13/09/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.440 - Slide rail, 1 U, static installation for VX IT, TS IT, TX CableNet

For mounting between a front and a rear pair of mounting angles.

Features

Model No.	DK 5501.440
Product description	Side system punchings for mounting accessories and cooling components that expel to the side.
Benefits	Simply locate into the system punchings of the 482.6 mm (19") mounting brackets after adjusting the required 482.6 mm (19") distance between levels
Applications	For mounting on the front mounting level To support heavy installed equipment
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Distance between mounting levels	645 mm
Length	575 mm
Installation options	for 482.6 mm (19") mounting angles, standard
Assembly instruction	The 482.6 mm (19") spacing between levels in the VX IT must be adjusted accordingly prior to installation
Load capacity	800 N, static
Note	Effective contact surface 35 mm per side
Contact surface	Width: 35 mm
To fit	Enclosure type: VX IT TS IT TX CableNet
Packs of	2 pc(s).
Net weight	1.6

Features

Gross weight	1.74
PCF per pack (cradle-to-gate)	5.9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177678996
E-Number Sweden	E7239694
ETIM 9	EC002620
ECLASS 8.0	27189261