

Rittal – The System.

Faster – better – everywhere.



DK 5501.450

Slide rail, 1 U, static installation

State: 15/08/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.450 - Slide rail, 1 U, static installation for VX IT, TS IT, TX CableNet

For mounting between a front and a rear pair of mounting angles.

Features

| | |
|----------------------------------|---|
| Model No. | DK 5501.450 |
| Product description | Side system punchings for mounting accessories and cooling components that expel to the side. |
| Benefits | Simply locate into the system punchings of the 482.6 mm (19") mounting brackets after adjusting the required 482.6 mm (19") distance between levels |
| Applications | For mounting on the front mounting level To support heavy installed equipment |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Distance between mounting levels | 745 mm |
| Length | 675 mm |
| Installation options | for 482.6 mm (19") mounting angles, standard |
| Assembly instruction | The 482.6 mm (19") spacing between levels in the VX IT must be adjusted accordingly prior to installation |
| Load capacity | 800 N, static |
| Note | Effective contact surface 35 mm per side |
| Contact surface | Width: 35 mm |
| To fit | Enclosure type: VX IT TS IT |
| Packs of | 2 pc(s). |
| Net weight | 1.8 |

Features

| | |
|-------------------------------|--|
| Gross weight | 2.02 |
| PCF per pack (cradle-to-gate) | 7.6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177679009 |
| E-Number Sweden | E7239695 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |