

Rittal – The System.

Faster – better – everywhere.



CP 6106.500 Pedestal, open

State: 03/08/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6106.500 - Pedestal, open

Pedestal open, for post-installation cable entry with pre-assembled connectors.



Features

Model No.	CP 6106.500
Product description	The complete welded alternatives to the pedestal. For post-installation cable entry with pre-assembled connectors.
Material	Steel
Surface finish	Spray-finished
Colour	RAL 7035
Width base plate	400 mm
Height base plate	10 mm
Depth base plate	400 mm
Material thickness pedestal	3 mm
Pedestal tube cross-section depth	73 mm
Pedestal tube cross-section width	86 mm
Load capacity (static)	40 kg
Dimensions	Height: 1,095 mm
Packs of	1 pc(s).
Net weight	22.5

Features

Gross weight	22.691
PCF per pack (cradle-to-gate)	91.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177698468
ETIM 9	EC002534
ECLASS 8.0	27182604