

Rittal – The System.

Faster – better – everywhere.



TP 6703.600 Pedestals

State: 29/08/2025 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 6703.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

Features

| | |
|-------------------------------------|---|
| Model No. | TP 6703.600 |
| Material | Enclosure: Sheet steel 1.5 mm Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Sheet steel |
| Surface finish | Enclosure, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated |
| Colour | RAL 7035 |
| Supply includes | Enclosure open at top Door or double door with locking rod (with depth 400 mm at the front, with depth 500 mm at the front and rear) Mounting plate Gland plates |
| Dimensions mounting plate (W x H) | 1,499 mm x 625 mm |
| Number of doors | 2 |
| Dimensions | Width: 1,600 mm Height: 675 mm Depth: 400 mm |
| IP protection category to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Note | Positioning slide VX 5051.172 can be used as a mounting aid for base/plinth system VX in its new design |
| Packs of | 1 pc(s). |

Features

| | |
|-----------------------|---------------|
| Net weight | 75 |
| Gross weight | 80 |
| Customs tariff number | 94032080 |
| EAN | 4028177959873 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |