

# Rittal – The System.

Faster – better – everywhere.



## TP 6707.600 Pedestals

State: 24/08/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TP 6707.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | TP 6707.600   |
| Material                            | Enclosure: Sheet steel 1.5 mm<br>Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in PU seal<br>Mounting plate: Sheet steel                                  |
| Surface finish                      | Enclosure, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint<br>Mounting plate: Zinc-plated  |
| Colour                              | RAL 7035  |
| Supply includes                     | Enclosure open at top<br>Door or double door with locking rod (with depth 400 mm at the front, with depth 500 mm at the front and rear)<br>Mounting plate<br>Gland plates |
| Dimensions mounting plate (W x H)   | 1,499 mm x 571 mm   |
| Number of doors                     | 2   |
| Dimensions                          | Width: 1,600 mm<br>Height: 675 mm<br>Depth: 500 mm  |
| IP protection category to IEC 60529 | IP 55   |
| Protection category NEMA            | NEMA 12   |
| Note                                | Mounting plate, depth-variable on a 25 mm pitch pattern   |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 85  |

# Features

|                       |               |
|-----------------------|---------------|
| Gross weight          | 90            |
| Customs tariff number | 94032080      |
| EAN                   | 4028177959910 |
| ETIM 9                | EC000784      |
| ETIM 8                | EC000784      |
| ECLASS 8.0            | 27180504      |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |