

Rittal – The System.

Faster – better – everywhere.



CX 6720.000

CX console

State: 12/09/2025 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CX 6720.000 - CX console

Four widths create the ideal conditions for individual monitoring and three-piece assembly of the CX console system.



Features

Model No.	CX 6720.000
Design	Console
Product description	Four widths create the ideal conditions for individual monitoring and three-piece assembly of the CX console system.
Material	Enclosure: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm, all-round foamed-in PU seal
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint
Colour	RAL 7035
Supply includes	Enclosure Cover hinged at bottom, including cover retainer Open base for individual cable entry Lock: 3 mm double-bit
Dimensions	Width: 600 mm Height: 515 mm
Depth (top)	125 mm
Depth (bottom)	245 mm
IK Code	IK10
Note	A desk unit and pedestal are required for a 3-part console assembly.

Features

IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 1 NEMA 12
Basic material	Sheet steel
Dimensions	Width: 600 mm Height: 515 mm Depth (top): 125 mm Depth (bottom): 245 mm
Number of locks	2
Lock version	Cam
Lock insert	3 mm double-bit
Lock	Lock version: Cam Number of locks: 2 Lock insert: 3 mm double-bit
Packs of	1 pc(s).
Net weight	15
Gross weight	16.8
Customs tariff number	94032080
EAN	4028177983687
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity