

Rittal – The System.

Faster – better – everywhere.



DK 7706.135

Wall-mounted enclosures EL, 3-part

State: 06/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7706.135 - Wall-mounted enclosures EL, 3-part with punched rails and mounting angles, depth-variable

Wall-mounted enclosure 3-part, pre-configured with: Solid gland plate, top and bottom, punched rails, C rails, wall mounting bracket. Protection category IP 55.

Features

Model No.	DK 7706.135
Design	Wall-mounted enclosures IT with punched rails and mounting angles, depth-variable
Product description	Wall-mounted enclosure with optimum accessibility due to hinged part.
Material	Wall and hinged part: Sheet steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General colour	RAL 7035
Colour	Wall and hinged part: RAL 7035 Glazed door: RAL 7035/7015 (slate grey)
Supply includes	Wall section with solid gland plate, top and bottom, two vertical mounting rails and C rail, horizontal, for cable clamping Hinged part with 25 mm pitch pattern of holes in the front and rear frame, and two 482.6 mm (19") mounting angles at the front, infinitely depth-variable 4 wall mounting brackets 10 mm Designer glazed door 1 double-kit key no. 5 Mini-comfort handle for lock inserts Security lock 3524 E
Units	6 U
Dimensions	Width: 600 mm Height: 345 mm Depth: 473 mm
Installation depth	420 mm

Features

Clearances	Clearance width: 502 mm Clearance height: 282 mm
Depth hinged part	316 mm
Depth of wall section	135 mm
IK Code	IK08
Load capacity of hinged part (static)	300 N
Basic material	Sheet steel
Protection category to IEC 60 529	IP 55
Packs of	1 pc(s).
Net weight	25.4 kg
Gross weight	26.4 kg
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27142408
Product description	DK Wall-mounted enclosures, 3-part, WHD: 600x345x473 mm, 6 U, With punched rails, and mounting angles, depth-variable

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

Tender text

Pre-assembled wall-mounted distributor, 6 U

Enclosure:

Three-part wall-mounted distributor enclosure,
consisting of:

Wall-mounted with 2 vertical mounting rails and one horizontally mounted C rail for cable clamping, top and bottom gland plates can be exchanged, solid, hinged part with two infinitely adjustable 482.6 mm (19") mounting angles, mounted on C rails, with all-round 25 mm punched profile in front and rear frames, glazed door design with mini comfort handle for lock inserts, with 3524E security lock that can be changed for mini comfort handle for semi-cylinder (option), 4 x 10 mm wall-mounting brackets included.

Protection category: IP 55 to EN 60 529/10.91

Hinged part load capacity: 30 kg

Material:

Enclosure: Sheet steel 1.5 mm

Viewing window: 3 mm single-pane safety glass

Surface finish:

Electrophoretic dipcoat, spray finished,
enclosure RAL 7035, glazed door RAL 7035/7015

Dimensions (W x H x D):

600 x 345 x 473 mm, 6 U