
## Rittal - The System.

Faster – better – everywhere.





# DK 7706.135 Wall-mounted enclosures EL, 3-part

State: 28/11/2025 (Source: rittal.com/sg-en)



# DK 7706.135 - Wall-mounted enclosures EL, 3-part with punched rails and mounting angles, depth-variable

Wall-mounted enclosure 3-part, pre-configured with: Solid gland plate, top and bottom, punched rails, C rails, wall mounting bracket. Protection category IP 55.

#### **Features**

| Model No.           | DK 7706.135   |
|---------------------|---|
| Design              | Wall-mounted enclosures IT  |
|                     | with punched rails and mounting angles, depth-variable                |
| Product description | Wall-mounted enclosure with optimum accessibility due to hinged part. |
| Material            | Wall and hinged part: Sheet steel, 1.5 mm                             |
|                     | Viewing window: Single-pane safety glass, 3 mm                        |
| Surface finish      | Powder-coated   |
| General colour      | RAL 7035  |
| Colour              | Wall and hinged part: RAL 7035  |
|                     | Glazed door: RAL 7035/7015 (slate grey)                               |
| Supply includes     | Wall section with solid gland plate, top and bottom, two vertical     |
|                     | mounting rails and C rail, horizontal, for cable clamping             |
|                     | Hinged part with 25 mm pitch pattern of holes in the front and rear   |
|                     | frame, and two 482.6 mm (19") mounting angles at the front,           |
|                     | infinitely depth-variable   |
|                     | 4 wall mounting brackets 10 mm  |
|                     | Designer glazed door  |
|                     | 1 double-kit key no. 5  |
|                     | Mini-comfort handle for lock inserts                                  |
|                     | Security lock 3524 E  |
| Units               | 6 U   |
| Dimensions          | Width: 600 mm   |
|                     | Height: 345 mm  |
|                     | Depth: 473 mm   |
| Installation depth  | 420 mm  |

© Rittal 2025

### Features

| Clearances                            | Clearance width: 502 mm<br>Clearance height: 282 mm |
|---------------------------------------|---|
| Depth hinged part                     | 316 mm  |
| Depth of wall section                 | 135 mm  |
| IK Code                               | IK08  |
| Load capacity of hinged part (static) | 300 N   |
| Basic material                        | Sheet steel   |
| Protection category to IEC 60 529     | IP 55   |
| Packs of                              | 1 pc(s).  |
| Net weight                            | 25.4  |
| Gross weight                          | 26.4  |
| Customs tariff number                 | 94032080  |
| EAN                                   | 4028177324176                                       |
| ETIM 9                                | EC000261  |
| ECLASS 8.0                            | 27142408  |

# **Approvals**

Approvals UL + C-UL (listed)

© Rittal 2025 3

#### Tender text

Pre-assembled wall-mounted distributor, 6 U

#### **Enclosure:**

Three-part wall-mounted distributor enclosure, consisting of:

Wall-mounted with 2 vertical mounting rails and one horizontally mounted C rail for cable clamping, top and bottom gland plates can be exchanged, solid, hinged part with two infinitely adjustable 482.6 mm (19") mounting angles, mounted on C rails, with all-round 25 mm punched profile in front and rear frames, glazed door design with mini comfort handle for lock inserts, with 3524E security lock that can be changed for mini comfort handle for semi-cylinder (option), 4 x 10 mm wall-mounting brackets included.

Protection category: IP 55 to EN 60 529/10.91

Hinged part load capacity: 30 kg

Material:

Enclosure: Sheet steel 1.5 mm

Viewing window: 3 mm single-pane safety glass

Surface finish:

Electrophoretic dipcoat, spray finished,

enclosure RAL 7035, glazed door RAL 7035/7015

Dimensions (W x H x D): 600 x 345 x 473 mm, 6 U

© Rittal 2025 4