

# Rittal – The System.

Faster – better – everywhere.



## DK 7721.535

## Wall-mounted enclosures EL, 3-part

State: 25/08/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7721.535 - Wall-mounted enclosures EL, 3-part pre-configured with mounting angles, depth-variable

Wall-mounted enclosure 3-part, pre-configured with: Solid gland plate, top, with brush strip at the bottom, mounting rails, C rails, outlet filter, earth rail, wall-mounting bracket

## Features

|                     |  |
|---------------------|--|
| Model No.           | DK 7721.535  |
| Design              | Wall-mounted enclosures IT<br>pre-configured with mounting angles, depth-variable  |
| Product description | Wall-mounted enclosure with optimum accessibility due to hinged part.  |
| Material            | Wall and hinged part: Sheet steel, 1.5 mm<br>Viewing window: Single-pane safety glass, 3 mm  |
| Surface finish      | Powder-coated  |
| General colour      | RAL 7035   |
| Colour              | Wall and hinged part: RAL 7035<br>Glazed door: RAL 7035/7015 (slate grey)  |
| Supply includes     | Wall section with solid gland plate at the top and brush strip at the bottom, two vertical mounting rails and C rail, horizontal, for cable clamping<br>Hinged part with 25 mm pitch pattern of holes in the front and rear frame, two 482.6 mm (19") mounting angles at the front, infinitely depth-variable, and side outlet filters on the left and right<br>Earth rail with star earthing<br>Designer glazed door<br>1 double-kit key no. 5<br>Wall mounting bracket, 10 mm, reinforced<br>Comfort handle for lock inserts and 2-point locking<br>Security lock 3524 E |
| Units               | 21 U   |

## Features

|                                       |  |
|---------------------------------------|--|
| Dimensions                            | Width: 600 mm<br>Height: 1,012 mm<br>Depth: 673 mm         |
| Installation depth                    | 620 mm   |
| Clearances                            | Clearance width: 502 mm<br>Clearance height: 949 mm        |
| Depth hinged part                     | 516 mm   |
| Depth of wall section                 | 135 mm   |
| IK Code                               | IK08   |
| Load capacity of hinged part (static) | 750 N  |
| Basic material                        | Sheet steel  |
| Protection category to IEC 60 529     | IP 54 in conjunction with solid gland plate top and bottom |
| Packs of                              | 1 pc(s).   |
| Net weight                            | 57   |
| Gross weight                          | 59   |
| Customs tariff number                 | 94032080   |
| EAN                                   | 4028177551039  |
| E-Number Sweden                       | E7239962   |
| ETIM 9                                | EC000261   |
| ECLASS 8.0                            | 27142408   |

## Approvals

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|