

# Rittal – The System.

Faster – better – everywhere.



## DK 7824.222

### Glazed door, vented

State: 02/08/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7824.222 - Glazed door, vented for TS, TS IT, VX SE

To replace existing doors. With 180° hinges and swivel handle with security lock no. 3524 E.

## Features

Model No.	DK 7824.222
Product description	Surface perforated on both sides with air inlet openings > 78% for optimum air throughput.
Material	Door: Sheet steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Glazed door, vented Comfort handle for profile half-cylinders with security lock 3524 E 180° hinges (4) Assembly parts
Assembly instruction	For TS enclosure suites with sheet steel doors, only the 180° hinge 7824.520 may be used.
To fit	Enclosure type: TS TS IT SE Width: 800 mm Height: 2,200 mm
Packs of	1 pc(s).
Net weight	22
Gross weight	22.6
Customs tariff number	94039910
EAN	4028177234208
ETIM 9	EC000747
ECLASS 8.0	27182204

# Tender text

Glazed door, vented, for TS

Glazed door, vented, made from 1.5 mm sheet steel  
with side slotted surfaces in RAL 7035,  
with foamed-in seal, 180° hinges,  
3 mm thick single-pane safety glass, 4-point latch  
locking rod, comfort handle with security lock no.  
3524 E. A semi-cylinder (40/45 mm) to DIN 18254  
may be inserted.

Hinges with captive hinge pins,  
door hinge may be swapped from right to left without  
dismantling locking rods. Door opening angle 180°.

Material: Sheet steel

Pane: Safety glass, 3 mm

Colour:

Frame: RAL 7035

Pane: Tinted, parsol grey

Dimensions: For enclosures (WxH): W: 800 mm H: 2200 mm