

Rittal – The System.

Faster – better – everywhere.



TS 8610.800 Glazed door

State: 22/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8610.800 - Glazed door for TS 8

Glazed doors for TS 8 instead of a sheet steel door or rear panel.



Features

Model No.	TS 8610.800
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section Corner pieces: Die-cast zinc Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	RAL 7035 Viewing window (printed mask on the inside): RAL 7015
Supply includes	Viewing door frame with safety glass Locking rod with double-bit insert 180° hinges (4) Visible area: W – 140 mm, H – 160 mm.
Visible area	Viewing window width: 640 mm Viewing window height: 1,840 mm
Viewing window height	1,840 mm

Features

IP protection category to IEC 60529	IP 55
To fit	Enclosure type: DK-TS TS 8 SE Width: = 800 mm Height: = 2,000 mm
Packs of	1 pc(s).
Net weight	33.25 kg
Gross weight	35 kg
Customs tariff number	76101000
ECLASS 8.0	27182204

Tender text

Glazed door for TS

Glazed door made of extruded aluminium section in RAL 7035, with foamed-in seal, 180° hinge, 3 mm thick single-pane safety glass, locking rod with four-point latching, with standard double-bit insert.

Double-bit insert can be exchanged for all lock inserts or comfort handles

(in connection with handle adaptor TS 8611.080).

Hinges with captive hinge pins, door hinge may be swapped from right to left without dismantling locking rods.

Material:

Frame: Sturdy extruded aluminium section, die-cast zinc corner pieces.

Pane: Single pane safety glass (ESG), 3 mm

Colour:

Frame: RAL 7035

Printed mask on the inside of the pane: RAL 7015

Protection category to EN 60 529/10.91: IP 55

Dimensions:

For enclosures (WxH): W: 800 mm H: 2000 mm