

# Rittal – The System.

Faster – better – everywhere.



## TS 8614.240 Partial mounting plates

State: 23/05/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8614.240 - Partial mounting plates for TS, VX SE

For universal interior installation and additional mounting levels.



## Features

|                     |  |
|---------------------|--|
| Model No.           | TS 8614.240  |
| Product description | For universal interior installation, also in conjunction with punched sections with mounting flanges and support strips. Defective assemblies are quickly and easily replaced. Additional mounting levels.   |
| Material            | Sheet steel, 2.5 mm  |
| Surface finish      | Zinc-plated  |
| Supply includes     | Assembly parts   |
| Note                | Partial mounting plates are fastened directly onto the vertical enclosure sections via the inner mounting level using the assembly parts supplied loose. In this mounting position (in both the width and the depth) they form one level with TS punched sections with mounting flanges 17 x 73 mm and TS support strips for the inner mounting level. |
| Dimensions          | Width: 1,100 mm<br>Height: 300 mm  |

# Features

---

|                       |   |
|-----------------------|---|
| To fit enclosure type | TS<br>VX SE   |
| To fit                | Enclosure type: TS<br>VX SE<br>Width: = 400 mm<br>= 1,200 mm<br>Depth: = 400 mm |
| Packs of              | 1 pc(s).  |
| Net weight            | 8.26 kg   |
| Gross weight          | 8.46 kg   |
| Customs tariff number | 94039910  |
| ETIM 9                | EC000213  |
| ECLASS 8.0            | 27409216  |
| Product description   | TS Partial mounting plate, for TS, SE, W/DH: 1100x300 mm                        |