

Rittal – The System.

Faster – better – everywhere.



TS 8614.880 Partial mounting plates

State: 14/07/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8614.880 - Partial mounting plates for TS, VX SE

For universal interior installation and additional mounting levels.



Features

Model No.	TS 8614.880
Product description	For universal interior installation, also in conjunction with punched sections with mounting flanges and support strips. Defective assemblies are quickly and easily replaced. Additional mounting levels.
Material	Sheet steel, 2.5 mm
Surface finish	Zinc-plated
Supply includes	Assembly parts
Note	Partial mounting plates are fastened directly onto the vertical enclosure sections via the inner mounting level using the assembly parts supplied loose. In this mounting position (in both the width and the depth) they form one level with TS punched sections with mounting flanges 17 x 73 mm and TS support strips for the inner mounting level.
Dimensions	Width: 700 mm Height: 700 mm

Features

To fit	Enclosure type: TS VX SE Width: = 800 mm Depth: = 800 mm
Packs of	1 pc(s).
Net weight	11.271
Gross weight	11.864
Customs tariff number	94039910
EAN	4028177212374
ETIM 9	EC000213
ECLASS 8.0	27409216