

Rittal – The System.

Faster – better – everywhere.



SV 9393.571 Current transformer

State: 01/06/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9393.571 - Current transformer

Features

| | |
|-----------------------------------|---|
| Model No. | SV 9393.571 |
| Design | Output voltage 333 mV |
| Material | Polyamide Fire protection corresponding to UL 94 |
| Colour | RAL 9005 |
| Supply includes | 2 plug-in feet 4 insulating caps 2 primary bar clamps 4 grub screws |
| To fit busbars | 2 x 100 x 10 80 x 60 50 x 80 |
| Primary current | 2,000 A |
| Standards | EN 61869-1/ 2 EN 42600 VDE 0100 EN 50274 / VDE 0660-514 DGUV regulation 3 |
| Dimensions | Width: 129 mm Height: 156 mm Depth: 30 mm |
| Operating temperature range | -5 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Ambient humidity (non-condensing) | 10...90 % |
| Fundamental frequency | 50...60 Hz |
| Accuracy Class | 0.5 |
| Insulation material (class) | F |

Features

| | |
|-----------------------|--------------------------------------|
| Packs of | 1 pc(s). |
| Net weight | 0.545 kg |
| Gross weight | 0.554 kg |
| Customs tariff number | 85043129 |
| ETIM 9 | EC002048 |
| Product description | SV Current transformer 2000 A, 85 mm |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|
