

Rittal – The System.

Faster – better – everywhere.



PK 9521.050

Polycarbonate enclosures PK

State: 27/01/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9521.050 - Polycarbonate enclosures PK with knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

Model No.	PK 9521.050
Design	PK enclosure with solid cover
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

Features

Dimensions	Width: 254 mm Height: 180 mm Depth: 111 mm
------------	--

Cable entry (quantity x diameter)	M20 M25/M32 M32/M40
-----------------------------------	---------------------------

No. of metric knockouts	24 x M20 4 x M25/M32 4 x M32/M40
-------------------------	--

Operating temperature range	-35 °C...80 °C
-----------------------------	----------------

Basic material	Polycarbonate
----------------	---------------

Packs of	1 pc(s).
----------	----------

Net weight	0.849
------------	-------

Gross weight	0.91
--------------	------

Customs tariff number	94037000
-----------------------	----------

EAN	4028177490215
-----	---------------

ETIM 9	EC000261
--------	----------

ECLASS 8.0	27180101
------------	----------

Approvals

Approvals	C-UL DNV-GL UL
-----------	----------------------

Explanations	Declaration of conformity
--------------	---------------------------

Tender text

Polycarbonat-Gehäuse mit Vorprägungen

Polycarbonate enclosure with solid cover with knockouts

Enclosure: Fibreglass-reinforced polycarbonate
with knockouts for cable entry

Cover: Fibreglass-reinforced polycarbonate
all-round foamed-in PU seal

Cover screws: Polyamide

Insulating bungs: Polyethylene

Supply includes: Cover screws

Insulating bungs for wall mounting screws

Accessories: Wall mounting bracket

Protection category to IEC 60 529: IP 66

Protection category NEMA: NEMA 4X

Colour: similar to RAL 7035

Dimensions (W x H x T): 254 x 180 x 111 mm