

Rittal – The System.

Faster – better – everywhere.



SV 9630.000

Mini-PLS bus-mounting fuse bases

State: 03/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9630.000 - Mini-PLS bus-mounting fuse bases

Rated current 63 A



Features

Model No.	SV 9630.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 9011 Cover: RAL 7035
Note	Wire end ferrules should be used with fine wire conductors
Type of electrical connection	Box terminal
Fuse inserts	D 02-E 18 (adaptor sleeve)
Rated operating voltage	400 V
Rated current max.	63 A
Dimensions	Width: 38 mm Height: 160 mm
Connection of round conductors	1.5 - 16 mm ²
Packs of	1 pc(s).
Net weight	0.3 kg
Gross weight	0.316 kg
Copper weight (kg per piece)	0.11

Features

Customs tariff number	85369095
ETIM 9	EC001644
ECLASS 8.0	27142120
Product description	SV Mini-PLS bus-mounting fuse base, D02-E18, 63 A, 400 V, 3-pole, round conductor connection 1,5-16 mm ² , adaptor sleeve, including cover plate

Approvals

Explanations	Declaration of conformity
--------------	---------------------------