Rittal – The System.

Faster – better – everywhere.





AE 1003.600 Compact enclosures AE

State: 17.11.2025 (Source: rittal.com/si-sl)



AE 1003.600 - Compact enclosures AE Stainless steel

Compact enclosure AE in stainless steel including mounting plate.

Features

Model No.	AE 1003.600
Material	Enclosure: Stainless steel
	Door: Stainless steel, all-round foamed-in PU seal
	Mounting plate: Sheet steel
	Stainless steel 1.4301 (AISI 304)
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height
	< 0.8 µm
	Mounting plate: Zinc-plated
Supply includes	Enclosure with door(s)
	Mounting plate
	Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 300 mm
	Height: 300 mm
	Depth: 210 mm
Dimensions mounting plate (W x H)	254 mm x 275 mm
Number of doors	1
Number of locks	1
Lock	Lock version: Cam
	Number of locks: 1
	Lock insert: 3 mm double-bit
	Material lock: Die-cast zinc, nickel-plated
Basic material	Stainless steel 1.4301 (AISI 304)

© Rittal 2025

Features

Net weight	6.45
Gross weight	6.76
Customs tariff number	94032080
EAN	4028177583924
E-Number Sweden	E3404509
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	DNV-GL UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3