

# Rittal – The System.

Faster – better – everywhere.



## AE 1008.600

## Kompaktna ohišja AE

State: 20.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1008.600 - Kompaktna ohišja AE Nerjavno jeklo

Kompaktno AE ohišje iz nerjavnega jekla, vključno z montažno ploščo.

## Features

|                              |   |
|------------------------------|---|
| Št. Modela                   | AE 1008.600   |
| Material                     | Ohišje: nerjavno jeklo<br>Vrata: nerjavno jeklo, penasto PU tesnilo po celotnem obodu<br>Montažna plošča: jeklena pločevina<br>Nerjavno jeklo 1.4301 (AISI 304) |
| Površinska obdelava          | Ohišje in vrata: brušena površina, zrnatost 400, hrapavost površine < 0,8 µm<br>Montažna plošča: pocinkana  |
| Obseg dobave                 | Ohišje z vrati<br>Montažna plošča<br>Ključavnica: 3 mm dvojna ključavnica   |
| Razred zaščite NEMA          | NEMA 4X   |
| Razred zaščite po IEC 60 529 | IP 66   |
| IK koda                      | IK08  |
| Mere                         | Širina: 380 mm<br>Višina: 600 mm<br>Globina: 210 mm   |
| Mere montažne plošče (Š x V) | 334 mm x 570 mm   |
| Število vrat                 | 1   |
| Število ključavnic           | 2   |
| Zaklepanje                   | Različica ključavnice: Ključavnica<br>Število ključavnic: 2<br>Vložek ključavnice: 3 mm dvojni nastavek<br>Material lock: tlačno liti cink, nikljano            |
| Osnovni material             | Stainless steel 1.4301 (AISI 304)   |
| Paketi                       | 1 pc(s).  |
| Neto teža                    | 14,25 kg  |

# Features

---

|                           |   |
|---------------------------|---|
| Bruto teža                | 14,48 kg  |
| Carinska tarifna številka | 94032080  |
| ETIM 9                    | EC000261  |
| ETIM 8                    | EC000261  |
| ECLASS 8.0                | 27180101  |
| Opis izdelka              | AE Compact enclosure, WHD: 380x600x210 mm, Stainless steel 1.4301, with mounting plate, single-door, with two cam locks |

---

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | DNV<br>Lloyds Register<br>UL + C-UL (listed)              |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---