

Rittal – The System.

Faster – better – everywhere.



AX 1011.000

Osnovno ohišje AX, nerjavno jeklo

State: 7.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 1011.000 - Osnovno ohišje AX, nerjavno jeklo

Ohišja so izdelana iz robustnega nerjavnega jekla in imajo integriran odmični sistem, ki omogoča obsežno razširitev sistema, hitro in varno, brez vrtanja.



Features

Št. Modela	AX 1011.000
Material	Ohišje: nerjavno jeklo Vrata: nerjavno jeklo, penasto PU tesnilo po celotnem obodu Montažna plošča: jeklena pločevina Nerjavno jeklo 1.4301 (AISI 304)
Površinska obdelava	Ohišje in vrata: brušena površina, zrnatost 400, hrapavost površine < 0,8 µm Montažna plošča: pocinkana
Obseg dobave	Ohišje z vrati, kot odpiranja 130° Montažna plošča Ključavnica: 3 mm dvojna ključavnica
Razred zaščite NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 4X NEMA 12
Razred zaščite po IEC 60 529	IP 66
Tipna ocena po UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12

Features

IK koda	IK10
Mere	Širina: 380 mm Višina: 300 mm Globina: 210 mm
Debelina materiala - vrata	1,5 mm
Debelina materiala - ohišje	1,25 mm
Debelina materiala montažne plošče	2 mm
Mere montažne plošče (Š x V)	330 mm x 275 mm
Število vrat	1
Zaklepanje	Različica ključavnice: Ključavnica Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek Material lock: Tlačno liti cink
Osnovni material	Stainless steel 1.4301 (AISI 304)
Paketi	1 pc(s).
Neto teža	7,1 kg
Bruto teža	7,532 kg
Carinska tarifna številka	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Opis izdelka	AX Compact enclosure, WHD: 380x300x210 mm, stainless steel 1.4301, with mounting plate, single-door, with one cam locks

Approvals

Approvals

Approvals

Bureau Veritas
DNV-GL
Lloyds Register of Shipping
UL + C-UL (listed)

Explanations

Declaration of conformity
PCF-declaration