

# Rittal – The System.

Faster – better – everywhere.



## AE 1013.600

## Kompaktna ohišja AE

State: 22.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1013.600 - Kompaktna ohišja AE Nerjavno jeklo

Kompaktno AE ohišje iz nerjavnega jekla, vključno z montažno ploščo.

## Features

Št. Modela	AE 1013.600
Material	Ohišje: nerjavno jeklo Vrata: nerjavno jeklo, penasto PU tesnilo po celotnem obodu Montažna plošča: jeklena pločevina Nerjavno jeklo 1.4301 (AISI 304)
Površinska obdelava	Ohišje in vrata: brušena površina, zrnatost 400, hrapavost površine < 0,8 µm Montažna plošča: pocinkana
Obseg dobave	Ohišje z vrati Montažna plošča Ključavnica: 3 mm dvojna ključavnica
Razred zaščite NEMA	NEMA 4X
Razred zaščite po IEC 60 529	IP 66
IK koda	IK08
Mere	Širina: 500 mm Višina: 500 mm Globina: 300 mm
Mere montažne plošče (Š x V)	449 mm x 470 mm
Število vrat	1
Število ključavnic	2
Zaklepanje	Različica ključavnice: Ključavnica Število ključavnic: 2 Vložek ključavnice: 3 mm dvojni nastavek Material lock: tlačno liti cink, nikljano
Osnovni material	Stainless steel 1.4301 (AISI 304)
Paketi	1 pc(s).
Neto teža	17,48 kg

## Features

---

Bruto teža	19,8 kg
Carinska tarifna številka	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Opis izdelka	AE Compact enclosure, WHD: 500x500x300 mm, Stainless steel 1.4301, with mounting plate, single-door, with two cam locks

---

## Approvals

---

Approvals	DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---