

# Rittal – The System.

Faster – better – everywhere.



## AE 1019.600

## Kompaktna ohišja AE

State: 7.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1019.600 - Kompaktna ohišja AE Nerjavno jeklo

Kompaktno AE ohišje iz nerjavnega jekla, vključno z montažno ploščo.

## Features

Št. Modela	AE 1019.600
Material	Ohišje: nerjavno jeklo Vrata: nerjavno jeklo, penasto PU tesnilo po celotnem obodu Montažna plošča: jeklena pločevina Nerjavno jeklo 1.4301 (AISI 304)
Površinska obdelava	Ohišje in vrata: brušena površina, zrnatost 400, hrapavost površine < 0,8 µm Montažna plošča: pocinkana
Obseg dobave	Ohišje z vrati Montažna plošča Ključavnica: 3 mm dvojna ključavnica 3-točkovni sistem zaklepanja
Razred zaščite NEMA	NEMA 12
Razred zaščite po IEC 60 529	IP 55
IK koda	IK08
Mere	Širina: 1.000 mm Višina: 1.200 mm Globina: 300 mm
Mere montažne plošče (Š x V)	940 mm x 1.155 mm
Število vrat	2
Zaklepanje	Različica ključavnice: 3-točkovni sistem zaklepanja Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek Material lock: Nerjavno jeklo 1.4301 (AISI 304)
Osnovni material	Stainless steel 1.4301 (AISI 304)
Paketi	1 pc(s).
Neto teža	71,4 kg

# Features

---

Bruto teža	79,5 kg
Carinska tarifna številka	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Opis izdelka	AE Compact enclosure, WHD: 1000x1200x300 mm, Stainless steel 1.4301, with mounting plate, two-door, 3-point lock system

# Approvals

---

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK