

Rittal – The System.

Faster – better – everywhere.



AE 1039.500

Kompaktna ohišja AE

State: 22.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1039.500 - Kompaktna ohišja AE

Enclosure with door of sheet steel, spray-finished with mounting plate and gland plate in the base

Features

| | |
|------------------------------------|--|
| Št. Modela | AE 1039.500 |
| Material | Ohišje: jeklena pločevina Vrata: jeklena pločevina, penasto PU tesnilo po celotnem obodu |
| Površinska obdelava | Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana |
| Barva | RAL 7035 |
| Obseg dobave | Ohišje z vrati na tečajih, popolnoma zaprto Plošča(e) z uvodnicami v podnožju ohišja Montažna plošča Ključavnica: 3 mm dvojna ključavnica |
| Razred zaščite NEMA | NEMA 4 |
| Razred zaščite po IEC 60 529 | IP 66 |
| IK koda | IK08 |
| Mere | Širina: 600 mm Višina: 380 mm Globina: 210 mm |
| Debelina materiala - vrata | 1,5 mm |
| Debelina materiala - ohišje | 1,38 mm |
| Debelina materiala montažne plošče | 2,5 mm |
| Mere montažne plošče (Š x V) | 549 mm x 355 mm |
| Število vrat | 1 |
| Zamenljiv tečaj vrat | Yes |
| Število ključavnic | 1 |

Features

| | |
|-----------------------------|---|
| Zaklepanje | Različica ključavnice: Ključavnica Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek |
| Plošča za kableske uvodnice | Velikost: 5 Količina: 1 |
| Osnovni material | Sheet steel |
| Paketi | 1 pc(s). |
| Neto teža | 14,274 kg |
| Bruto teža | 15,025 kg |
| Carinska tarifna številka | 94032080 |
| ECLASS 8.0 | 27180101 |
| Opis izdelka | AE Compact enclosure, WHD: 600x380x210 mm, Sheet steel, with mounting plate, single-door, with one cam lock |

Approvals

| | |
|--------------|---|
| Approvals | DNV Lloyds Register UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |