


Rittal – The System.

Faster – better – everywhere.



AE 1054.500

Kompaktna ohišja AE

State: 6.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1054.500 - Kompaktna ohišja AE

Enclosure with door of sheet steel, spray-finished with mounting plate and gland plate in the base

Features

Št. Modela	AE 1054.500
Material	Ohišje: jeklena pločevina Vrata: jeklena pločevina, penasto PU tesnilo po celotnem obodu
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana
Barva	RAL 7035
Obseg dobave	Ohišje z vrati na tečajih, popolnoma zaprto Plošča(e) z uvodnicami v podnožju ohišja Montažna plošča Ključavnica: 3 mm dvojna ključavnica
Razred zaščite NEMA	NEMA 4
Razred zaščite po IEC 60 529	IP 66
IK koda	IK08
Mere	Širina: 600 mm Višina: 600 mm Globina: 250 mm
Debelina materiala - vrata	1,75 mm
Debelina materiala - ohišje	1,5 mm
Debelina materiala montažne plošče	2,5 mm
Mere montažne plošče (Š x V)	549 mm x 570 mm
Število vrat	1
Zamenljiv tečaj vrat	Yes
Število ključavnic	2

Features

Zaklepanje	Različica ključavnice: Ključavnica Število ključavnic: 2 Vložek ključavnice: 3 mm dvojni nastavek
Plošča za kableske uvodnice	Velikost: 5 Količina: 1
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	23,278 kg
Bruto teža	24,7 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180101
Opis izdelka	AE Compact enclosure, WHD: 600x600x250 mm, Sheet steel, with mounting plate, single-door, with two cam locks

Approvals

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK