

Rittal – The System.

Faster – better – everywhere.



AE 1114.500

Kompaktna ohišja AE

State: 21.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1114.500 - Kompaktna ohišja AE

Enclosure with door of sheet steel, spray-finished with mounting plate and gland plate in the base

Features

| | |
|------------------------------------|--|
| Št. Modela | AE 1114.500 |
| Material | Ohišje: jeklena pločevina Vrata: jeklena pločevina, penasto PU tesnilo po celotnem obodu |
| Površinska obdelava | Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana |
| Barva | RAL 7035 |
| Obseg dobave | Ohišje z vrati na tečajih, popolnoma zaprto Plošča(e) z uvodnicami v podnožju ohišja Montažna plošča Ključavnica: 3 mm dvojna ključavnica 3-točkovni sistem zaklepanja |
| Razred zaščite NEMA | NEMA 12 |
| Razred zaščite po IEC 60 529 | IP 55 |
| IK koda | IK08 |
| Mere | Širina: 1.000 mm Višina: 1.400 mm Globina: 300 mm |
| Debelina materiala - vrata | 2 mm |
| Debelina materiala - ohišje | 1,5 mm |
| Debelina materiala montažne plošče | 3 mm |
| Mere montažne plošče (Š x V) | 940 mm x 1.355 mm |
| Število vrat | 2 |
| Zaklepanje | Različica ključavnice: 3-točkovni sistem zaklepanja Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek |

Features

| | |
|-----------------------------|--|
| Plošča za kableske uvodnice | Velikost: 4 Količina: 2 |
| Osnovni material | Sheet steel |
| Paketi | 1 pc(s). |
| Neto teža | 87,4 kg |
| Bruto teža | 92 kg |
| Carinska tarifna številka | 94032080 |
| ECLASS 8.0 | 27180101 |
| Opis izdelka | AE Compact enclosure, WHD: 1000x1400x300 mm, Sheet steel, with mounting plate, two-door, 3-point lock system |

Approvals

| | |
|--------------|---|
| Approvals | DNV Lloyds Register UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |