

Rittal – The System.

Faster – better – everywhere.



AE 1213.500

Kompaktna ohišja AE

State: 9.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1213.500 - Kompaktna ohišja AE

Enclosure with door of sheet steel, spray-finished with mounting plate and gland plate in the base

Features

Št. Modela	AE 1213.500
Material	Ohišje: jeklena pločevina Vrata: jeklena pločevina, penasto PU tesnilo po celotnem obodu
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana
Barva	RAL 7035
Obseg dobave	Ohišje z vrati na tečajih, popolnoma zaprto Plošča(e) z uvodnicami v podnožju ohišja Montažna plošča Ključavnica: 3 mm dvojna ključavnica 3-točkovni sistem zaklepanja
Razred zaščite NEMA	NEMA 12
Razred zaščite po IEC 60 529	IP 55
IK koda	IK08
Mere	Širina: 1.000 mm Višina: 1.200 mm Globina: 300 mm
Debelina materiala - vrata	2 mm
Debelina materiala - ohišje	1,5 mm
Debelina materiala montažne plošče	3 mm
Mere montažne plošče (Š x V)	940 mm x 1.155 mm
Število vrat	2
Zaklepanje	Različica ključavnice: 3-točkovni sistem zaklepanja Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek

Features

Plošča za kableske uvodnice	Velikost: 4 Količina: 2
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	79 kg
Bruto teža	80,5 kg
Carinska tarifna številka	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Opis izdelka	AE Compact enclosure, WHD: 1000x1200x300mm, Sheet steel, with mounting plate, two-door, 3-point lock system

Approvals

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK