

Rittal – The System.

Faster – better – everywhere.



AX 1305.000

Osnovno ohišje AX, nerjavno jeklo

State: 14.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 1305.000 - Osnovno ohišje AX, nerjavno jeklo

Ohišja so izdelana iz robustnega nerjavnega jekla in imajo integriran odmični sistem, ki omogoča obsežno razširitev sistema, hitro in varno, brez vrtanja.



Features

Št. Modela	AX 1305.000
Material	Ohišje: nerjavno jeklo Vrata: nerjavno jeklo, penasto PU tesnilo po celotnem obodu Montažna plošča: jeklena pločevina Nerjavno jeklo 1.4404 (AISI 316L)
Površinska obdelava	Ohišje in vrata: brušena površina, zrnatost 400, hrapavost površine < 0,8 µm Montažna plošča: pocinkana
Obseg dobave	Ohišje z vrati, kot odpiranja 130° Montažna plošča Ključavnica: 3 mm dvojna ključavnica
Razred zaščite NEMA	NEMA 1 NEMA 12
Razred zaščite po IEC 60 529	IP 55
Tipna ocena po UL 50E	Type 1 Type 12
IK koda	IK10
Mere	Širina: 1.000 mm Višina: 1.200 mm Globina: 300 mm
Debelina materiala - vrata	2 mm

Features

Debelina materiala - ohišje	1,5 mm
Debelina materiala montažne plošče	2,5 mm
Mere montažne plošče (Š x V)	945 mm x 1.175 mm
Število vrat	2
Zaklepanje	Različica ključavnice: 3-točkovni sistem zaklepanja Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek Material lock: Tlačno liti cink
Osnovni material	Stainless steel 1.4404 (AISI 316L)
Paketi	1 pc(s).
Neto teža	71,4 kg
Bruto teža	76 kg
Carinska tarifna številka	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Opis izdelka	AX Compact enclosure, WHD: 1000x1200x300 mm, stainless steel 1.4404, with mounting plate, two-door, with 3-point lock system

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration