

# Rittal – The System.

Faster – better – everywhere.



## AE 1350.500

## Kompaktna ohišja AE

State: 7.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1350.500 - Kompaktna ohišja AE

Enclosure with door of sheet steel, spray-finished with mounting plate and gland plate in the base

## Features

Št. Modela	AE 1350.500
Material	Ohišje: jeklena pločevina Vrata: jeklena pločevina, penasto PU tesnilo po celotnem obodu
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana
Barva	RAL 7035
Obseg dobave	Ohišje z vrati na tečajih, popolnoma zaprto Plošča(e) z uvodnicami v podnožju ohišja Montažna plošča Ključavnica: 3 mm dvojna ključavnica
Razred zaščite NEMA	NEMA 4
Razred zaščite po IEC 60 529	IP 66
IK koda	IK08
Mere	Širina: 500 mm Višina: 500 mm Globina: 300 mm
Debelina materiala - vrata	1,75 mm
Debelina materiala - ohišje	1,5 mm
Debelina materiala montažne plošče	2,5 mm
Mere montažne plošče (Š x V)	449 mm x 470 mm
Število vrat	1
Zamenljiv tečaj vrat	Yes
Število ključavnic	2

# Features

---

Zaklepanje	Različica ključavnice: Ključavnica Število ključavnic: 2 Vložek ključavnice: 3 mm dvojni nastavek
Plošča za kableske uvodnice	Velikost: 4 Količina: 1
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	18,025 kg
Bruto teža	19,08 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180101
Opis izdelka	AE Compact enclosure, WHD: 500x500x300 mm, Sheet steel, with mounting plate, single-door, with two cam locks

# Approvals

---

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK