

Rittal – The System.

Faster – better – everywhere.



KL 1513.510

Priključne omarice KL

State: 10.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1513.510 - Priključne omarice KL brez kabelskih uvodnic

Spray-finished enclosure with sheet steel cover, without gland plate Protection category IP 66.



Features

| | |
|------------------------------|--|
| Št. Modela | KL 1513.510 |
| Material | Ohišje: jeklena pločevina Pokrov: jeklena pločevina, penasto PU tesnilo po celotnem obodu |
| Površinska obdelava | Ohišje in pokrov: temeljni premaz, prašno barvana zunanost, teksturirana barva |
| Barva | RAL 7035 |
| Obseg dobave | Ohišje s pokrovom Sponka za hitro odpiranje s plastičnimi pušami |
| Protection category NEMA | NEMA 4 |
| Razred zaščite po IEC 60 529 | IP 66 |
| IK koda | IK08 |
| Mere | Širina: 800 mm Višina: 400 mm Globina: 120 mm |
| Debelina materiala - pokrov | 1,25 mm |
| Debelina materiala - ohišje | 1,38 mm |
| Osnovni material | Sheet steel |
| Paketi | 1 pc(s). |

Features

| | |
|---------------------------|--|
| Neto teža | 10,458 kg |
| Bruto teža | 11,007 kg |
| Carinska tarifna številka | 73269098 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Opis izdelka | KL Terminal box, WHD: 800x400x120 mm, Sheet steel, without mounting plate, with cover, without gland plate |

Approvals

| | |
|--------------|--|
| Approvals | Bureau Veritas DNV Lloyds Register UL + C-UL (listed) |
| Explanations | Manufacturer's declaration Declaration of conformity UK |