

Rittal – The System.

Faster – better – everywhere.



KL 1518.510

Priključne omarice KL

State: 10.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1518.510 - Priključne omarice KL brez kabelskih uvodnic

Spray-finished enclosure with sheet steel cover, without gland plate Protection category IP 66.



Features

Št. Modela	KL 1518.510
Material	Ohišje: jeklena pločevina Pokrov: jeklena pločevina, penasto PU tesnilo po celotnem obodu
Površinska obdelava	Ohišje in pokrov: temeljni premaz, prašno barvana zunanost, teksturirana barva
Barva	RAL 7035
Obseg dobave	Ohišje s pokrovom Sponka za hitro odpiranje s plastičnimi pušami
Protection category NEMA	NEMA 4
Razred zaščite po IEC 60 529	IP 66
IK koda	IK08
Mere	Širina: 400 mm Višina: 200 mm Globina: 80 mm
Debelina materiala - pokrov	1,25 mm
Debelina materiala - ohišje	1,25 mm
Osnovni material	Sheet steel
Paketi	1 pc(s).

Features

Neto teža	2,783 kg
Bruto teža	2,983 kg
Carinska tarifna številka	73269098
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Opis izdelka	KL Terminal box, WHD: 400x200x80 mm, Sheet steel, without mounting plate, with cover, without gland plate

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
Explanations	Manufacturer's declaration Declaration of conformity UK