


Rittal – The System.

Faster – better – everywhere.



KL 1524.010

Priključne omarice KL

State: 8.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1524.010 - Priključne omarice KL Nerjavno jeklo

Priključne omarice, nerjavno jeklo 1.4301 (AISI 304), Razred zaščite IP 66.

Features

| | |
|------------------------------|--|
| Št. Modela | KL 1524.010 |
| Material | Ohišje: nerjavno jeklo 1.4301 (AISI 304) Pokrov: nerjavno jeklo 1.4301 (AISI 304), penasto PU tesnilo po celotnem obodu |
| Površinska obdelava | Ohišje in pokrov: brušeno, zrnatost 180 |
| Obseg dobave | Ohišje s pokrovom Sponka za hitro odpiranje s plastičnimi pušami |
| Protection category NEMA | NEMA 4X |
| Razred zaščite po IEC 60 529 | IP 66 |
| IK koda | IK08 |
| Mere | Širina: 300 mm Višina: 200 mm Globina: 80 mm |
| Debelina materiala - pokrov | 1,25 mm |
| Debelina materiala - ohišje | 1,25 mm |
| Zaklepanje | Število ključavnic: 4 |
| Osnovni material | Stainless steel 1.4301 (AISI 304) |
| Paketi | 1 pc(s). |
| Neto teža | 2,15 kg |
| Bruto teža | 2,28 kg |
| Carinska tarifna številka | 84879090 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Features

Opis izdelka

KL Terminal box, WHD: 300x200x80 mm, Stainless steel 1.4301, without mounting plate, with cover, without gland plate

Approvals

Approvals

Bureau Veritas
DNV-GL
Lloyds Register of Shipping
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK