

Rittal – The System.

Faster – better – everywhere.



KL 1529.010

Priključne omarice KL

State: 25.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1529.010 - Priključne omarice KL Nerjavno jeklo

Priključne omarice, nerjavno jeklo 1.4301 (AISI 304), Razred zaščite IP 66.

Features

Št. Modela	KL 1529.010
Material	Ohišje: nerjavno jeklo 1.4301 (AISI 304) Pokrov: nerjavno jeklo 1.4301 (AISI 304), penasto PU tesnilo po celotnem obodu
Površinska obdelava	Ohišje in pokrov: brušeno, zrnatost 180
Obseg dobave	Ohišje s pokrovom Sponka za hitro odpiranje s plastičnimi pušami
Protection category NEMA	NEMA 4X
Razred zaščite po IEC 60 529	IP 66
IK koda	IK08
Mere	Širina: 300 mm Višina: 200 mm Globina: 120 mm
Debelina materiala - pokrov	1,25 mm
Debelina materiala - ohišje	1,25 mm
Zaklepanje	Število ključavnic: 4
Osnovni material	Stainless steel 1.4301 (AISI 304)
Paketi	1 pc(s).
Neto teža	2,7 kg
Bruto teža	2,975 kg
Carinska tarifna številka	84879090
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Features

Opis izdelka

KL Terminal box, WHD: 300x200x120 mm, Stainless steel 1.4301, without mounting plate, with cover, without gland plate

Approvals

Approvals

Bureau Veritas
DNV
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK