

# Rittal – The System.

Faster – better – everywhere.



## KL 1535.510

## Priključne omarice KL

State: 21.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KL 1535.510 - Priključne omarice KL s kabelskimi uvodnicami

Spray-finished enclosure with sheet steel cover, with gland plate. Protection category IP 55.



## Features

|                              |   |
|------------------------------|---|
| Št. Modela                   | KL 1535.510   |
| Material                     | Ohišje: jeklena pločevina<br>Pokrov: jeklena pločevina, penasto PU tesnilo po celotnem obodu  |
| Površinska obdelava          | Ohišje in pokrov: temeljni premaz, prašno barvana zunanost, teksturirana barva  |
| Barva                        | RAL 7035  |
| Obseg dobave                 | Ohišje s pokrovom<br>Sponka za hitro odpiranje s plastičnimi pušami<br>Plošče s kabelskimi uvodnicami iz jeklene pločevine s tesnili in montažnimi deli |
| Protection category NEMA     | NEMA 12   |
| Razred zaščite po IEC 60 529 | IP 55   |
| IK koda                      | IK08  |
| Mere                         | Širina: 300 mm<br>Višina: 300 mm<br>Globina: 120 mm   |
| Debelina materiala - pokrov  | 1,25 mm   |
| Debelina materiala - ohišje  | 1,38 mm   |

## Features

|                           |   |
|---------------------------|---|
| Kabelske uvodnice         | Število prirobničnih plošč (leva + desna): 1 + 1<br>Size of gland plate for bus enclosures, position left/right: 2<br>Število prirobničnih plošč (zgornja + spodnja): 1 + 1<br>Size of gland plate for bus enclosures, position top/bottom: 2 |
| Osnovni material          | Sheet steel   |
| Paketi                    | 1 pc(s).  |
| Neto teža                 | 4,3 kg  |
| Bruto teža                | 4,47 kg   |
| Carinska tarifna številka | 73269098  |
| ECLASS 8.0                | 27180101  |
| Opis izdelka              | KL Terminal box, WHD: 300x300x120 mm, Sheet steel, without mounting plate, with cover, with gland plate   |

## Approvals

|              |  |
|--------------|--|
| Approvals    | Bureau Veritas<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity UK                                   |