
### Rittal - The System.

Faster – better – everywhere.





# KX 1541.000

# Terminal box KX, sheet steel, with gland plate

State: 4.11.2025 (Source: rittal.com/si-sl)



# KX 1541.000 - Terminal box KX, sheet steel, with gland plate

The small enclosure KX, terminal box KX, with a gland plate allows for flexible interior installation and simple cable entry with optimum use of space.







#### **Features**

Model No.	KX 1541.000
Material	Enclosure: Sheet steel Cover: Sheet steel, all-round foamed-in PU seal
Surface finish	Enclosure and cover: Dipcoat primed, powder-coated on the outside textured paint
Colour	RAL 7035
Supply includes	Enclosure with cover Mini cam locks Sheet steel gland plates with seals and assembly parts
Protection category NEMA	NEMA 1 NEMA 12
Protection category to IEC 60 529	IP 55
Type rating to UL 50E	Type 1 Type 12
IK Code	IK08

© Rittal 2025 2

#### **Features**

Dimensions	Width: 800 mm
	Height: 400 mm
	Depth: 120 mm
Material thickness - cover	1,25 mm
Material thickness - enclosure	1,25 mm
Gland plates	:1+1
	: 3 + 3
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	10.541
Gross weight	11.65
PCF per pack (cradle-to-gate)	44.6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	84879059
EAN	4028177816466
E-Number Sweden	E3465212
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

# Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Certificates	Protection category

© Rittal 2025 3

# **Approvals**

Explanations

Declaration of conformity Declaration of conformity UK PCF-declaration

© Rittal 2025