

Rittal – The System.

Faster – better – everywhere.



EB 1549.500

E-Box EB

State: 21.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EB 1549.500 - E-Box EB

Wall-mounted enclosure with door and mounting plate of sheet steel. Protection category IP 66. With 180° hinge. Lock insert may also be exchanged for individual lock systems.

Features

| | |
|------------------------------------|---|
| Št. Modela | EB 1549.500 |
| Material | Ohišje in vrata: jeklena pločevina, penasto PU tesnilo po celotnem obodu |
| Površinska obdelava | Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana |
| Barva | RAL 7035 |
| Obseg dobave | Ohišje z vrati na tečajih 180° tečaji Ključavnica z dvojnimi 3 mm vložkom Montažna plošča |
| Protection category NEMA | NEMA 4 |
| Razred zaščite po IEC 60 529 | IP 66 |
| IK koda | IK08 |
| Mere | Širina: 200 mm Višina: 200 mm Globina: 120 mm |
| Mere montažne plošče (Š x V) | 175 mm x 185 mm |
| Debelina materiala - ohišje | 1,25 mm |
| Debelina materiala - vrata | 1,25 mm |
| Debelina materiala montažne plošče | 2 mm |
| Zaklepanje | Različica ključavnice: Ključavnica Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek |
| Osnovni material | Sheet steel |

Features

| | |
|---------------------------|---|
| Paketi | 1 pc(s). |
| Neto teža | 2,415 kg |
| Bruto teža | 2,615 kg |
| Carinska tarifna številka | 94032080 |
| ECLASS 8.0 | 27180101 |
| Opis izdelka | EB E-Box, WHD: 200x200x120, Sheet steel, with mounting plate, with door |

Approvals

| | |
|--------------|---|
| Approvals | Bureau Veritas C-UL Lloyds Register UL UL + C-UL (listed) |
| Explanations | Manufacturer's declaration Declaration of conformity Declaration of conformity UK |