

Rittal – The System.

Faster – better – everywhere.



BG 1559.510

Priključna ohišja BG

State: 23.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



BG 1559.510 - Priključna ohišja BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

Features

Št. Modela	BG 1559.510
Material	Ohišje: jeklena pločevina Vrata: jeklena pločevina Nadzorno okno: polikarbonat, 4 mm
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva
Barva	RAL 7035
Obseg dobave	Ohišje z vrati Nadzorno okno v vratih Priključna plošča v podnožju ohišja
Protection category NEMA	NEMA 12
Razred zaščite po IEC 60 529	IP 65
IK koda	IK08
Mere	Širina: 600 mm Višina: 200 mm Globina: 125 mm
Debelina materiala - ohišje	1,25 mm
Debelina materiala - vrata	1,25 mm
Položaj tečajev vrat	bottom
Število podpornih tirnic	1
Zaklepanje	Različica ključavnice: Sponka za hitro odpiranje s plastičnimi pušami Število ključavnic: 3
Osnovni material	Sheet steel
Paketi	1 pc(s).

Features

Neto teža	5,066 kg
Bruto teža	5,333 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180101
Opis izdelka	BG Bus enclosure, WHD: 600x200x125 mm, Sheet steel, with gland plate in the base and support rails, Door with viewing window, hinged at bottom

Approvals

Approvals	Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity