


Rittal – The System.

Faster – better – everywhere.



EB 1578.500

E-Box EB

State: 21.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EB 1578.500 - E-Box EB

Wall-mounted enclosure with door and mounting plate of sheet steel. Protection category IP 66. With 180° hinge. Lock insert may also be exchanged for individual lock systems.

Features

Št. Modela	EB 1578.500
Material	Ohišje in vrata: jeklena pločevina, penasto PU tesnilo po celotnem obodu
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana
Barva	RAL 7035
Obseg dobave	Ohišje z vrati na tečajih 180° tečaji Ključavnica z dvojnimi 3 mm vložkom Montažna plošča
Protection category NEMA	NEMA 4
Razred zaščite po IEC 60 529	IP 66
IK koda	IK08
Mere	Širina: 300 mm Višina: 600 mm Globina: 155 mm
Mere montažne plošče (Š x V)	275 mm x 585 mm
Debelina materiala - ohišje	1,38 mm
Debelina materiala - vrata	1,25 mm
Debelina materiala montažne plošče	2 mm
Zaklepanje	Različica ključavnice: Ključavnica Število ključavnic: 2 Vložek ključavnice: 3 mm dvojni nastavek
Osnovni material	Sheet steel

Features

Paketi	1 pc(s).
Neto teža	9,5 kg
Bruto teža	9,9 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180101
Opis izdelka	EB E-Box, WHD: 300x600x155, Sheet steel, with mounting plate, with door

Approvals

Approvals	C-UL UL UL + C-UL (listed)
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK