# Rittal - The System.

Faster – better – everywhere.





EB 1579.500 E-Box EB

State: 4.11.2025 (Source: rittal.com/si-sl)



#### EB 1579.500 - E-Box EB

Wall-mounted enclosure with door and mounting plate of sheet steel. Protection category IP 66. With 180° hinge. Lock insert may also be exchanged for individual lock systems.

### **Features**

Model No.	EB 1579.500
Material	Enclosure and door: Sheet steel, all-round foamed-in PU seal
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure with hinged door 180° hinge Cam lock with 3 mm double-bit insert Mounting plate
Protection category NEMA	NEMA 4
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 300 mm Height: 800 mm Depth: 155 mm
Dimensions mounting plate (W x H)	275 mm x 785 mm
Material thickness - enclosure	1,38 mm
Material thickness - door	1,25 mm
Material thickness of mounting plate	2 mm
Lock	Lock version: Cam Number of locks: 2 Lock insert: 3 mm double-bit
Basic material	Sheet steel

© Rittal 2025

### Features

Packs of	1 pc(s).
Net weight	12.145
Gross weight	12.784
Customs tariff number	94032080
EAN	4028177251823
E-Number Sweden	E3404514
ECLASS 8.0	27180101

# **Approvals**

Approvals	C-UL
	UL
	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3