

Rittal – The System.

Faster – better – everywhere.



SZ 1590.010 Stenski nosilec

State: 27.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1590.010 - Stenski nosilec za AX jeklena pločevina, KX jeklena pločevina, AX IT, EL

Za namestitev AX in KX ohišij iz nerjavnega jekla.

Features

| | |
|-----------------------------------|--|
| Št. Modela | SZ 1590.010 |
| Opis izdelka | Za montažo ohišij AX in KX iz jeklene pločevine. |
| Prednosti | Neposredno privijanje z zadnje strani s samoreznim vijakom v prehod ohišja |
| Material | Jeklena pločevina, pocinkano |
| Obseg dobave | Sestavni deli |
| Razdalja od stene | 10 mm |
| Primerno za | Vrsta ohišja: AX sheet steel KX sheet steel AX wall-mounted enclosure, 3-part |
| Tipska ocena po UL 50E | Type 1 Type 3R Type 4 Type 12 |
| Paketi | 4 pc(s). |
| Neto teža | 0,132 kg |
| Bruto teža | 0,168 kg |
| PCF na paket (od zibelke do vrat) | 0,5 kg CO2 eq (Cat B) |
| Opomba o kategoriji PCF | Kategorija B: PCF vrednost (od zibelke do vrat) na podlagi teže izdelka, približno izračunana in samodeklarirana |
| Carinska tarifna številka | 83025000 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |

Features

Opis izdelka

SZ Wall mounting bracket, for AX and KX, sheet steel, wall distance:
10 mm

Approvals

Approvals

DNV
UL + C-UL - FTTA