

Rittal – The System.

Faster – better – everywhere.



SZ 1590.010 Stenski nosilec

State: 12.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1590.010 - Stenski nosilec za AX jeklena pločevina, KX jeklena pločevina, AX IT, EL

Za namestitev AX in KX ohišij iz nerjavnega jekla.

Features

Št. Modela	SZ 1590.010
Opis izdelka	Za montažo ohišij AX in KX iz jeklene pločevine.
Prednosti	Neposredno privijanje z zadnje strani s samoreznim vijakom v prehod ohišja
Material	Jeklena pločevina, pocinkano
Obseg dobave	Sestavni deli
Razdalja od stene	10 mm
Primerno za	Vrsta ohišja: AX sheet steel KX sheet steel AX wall-mounted enclosure, 3-part
Tipska ocena po UL 50E	Type 1 Type 3R Type 4 Type 12
Paketi	4 pc(s).
Neto teža	0,132 kg
Bruto teža	0,168 kg
PCF na paket (od zibelke do vrat)	0,5 kg CO2 eq (Cat B)
Opomba o kategoriji PCF	Kategorija B: PCF vrednost (od zibelke do vrat) na podlagi teže izdelka, približno izračunana in samodeklarirana
Carinska tarifna številka	83025000
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234

Features

Opis izdelka

SZ Wall mounting bracket, for AX and KX, sheet steel, wall distance:
10 mm

Approvals

Approvals

DNV
UL + C-UL - FTFA