


Rittal – The System.

Faster – better – everywhere.



BG 1606.520 Priključna ohišja BG

State: 25.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



BG 1606.520 - Priključna ohišja BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

Features

Št. Modela	BG 1606.520
Material	Ohišje: jeklena pločevina Vrata: jeklena pločevina Nadzorno okno: polikarbonat, 4 mm
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva
Barva	RAL 7035
Obseg dobave	Ohišje z vrati Nadzorno okno v vratih
Protection category NEMA	NEMA 12
Razred zaščite po IEC 60 529	IP 65
IK koda	IK08
Mere	Širina: 400 mm Višina: 300 mm Globina: 120 mm
Debelina materiala - ohišje	1,38 mm
Debelina materiala - vrata	1,25 mm
Položaj tečajev vrat	right
Število podpornih tirnic	1
Izrezi (količina x premer)	296
Zaklepanje	Različica ključavnice: Ključavnica Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek

Features

Kabelski vhod (količina x premer)	2 x M20 9 x M32 6 x M50
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	4,447 kg
Bruto teža	4,716 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180101
Opis izdelka	BG Bus enclosure, WHD: 400x300x120 mm, Sheet steel, with metric holes in the base and support rail, Door with viewing window, hinged on the right

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
