

# Rittal – The System.

Faster – better – everywhere.



## BG 1611.510

## Priključna ohišja BG

State: 23.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# BG 1611.510 - Priključna ohišja BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

## Features

Št. Modela	BG 1611.510
Material	Ohišje: jeklena pločevina Vrata: jeklena pločevina Nadzorno okno: polikarbonat, 4 mm
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva
Barva	RAL 7035
Obseg dobave	Ohišje z vrati Nadzorno okno v vratih
Protection category NEMA	NEMA 12
Razred zaščite po IEC 60 529	IP 65
IK koda	IK08
Mere	Širina: 400 mm Višina: 500 mm Globina: 160 mm
Debelina materiala - ohišje	1,38 mm
Debelina materiala - vrata	1,5 mm
Položaj tečajev vrat	right
Število podpornih tirnic	3
Izrezi (količina x premer)	33
Zaklepanje	Različica ključavnice: Ključavnica Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek
Kabelski vhod (količina x premer)	33 x M20

## Features

Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	7,39 kg
Bruto teža	7,779 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180101
Opis izdelka	BG Bus enclosure, WHD: 400x500x160 mm, Sheet steel, with metric holes in the base and support rail, Door with viewing window, hinged on the right

## Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity