

# Rittal – The System.

Faster – better – everywhere.



## AX 2262.140

## AX wall-mounted enclosure, 3-part

State: 16.9.2025 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2262.140 - AX wall-mounted enclosure, 3-part

The delivery concept of the three-part AX wall-mounted enclosures reduces complexity and enhances flexibility. The AX/VX modular system makes these enclosures suitable for a range of applications. The three-part structure ensures easy access.



## Features

|                 |  |
|-----------------|--|
| Model No.       | AX 2262.140  |
| Design          | Wall-mounted enclosures IT   |
| Material        | Wall and hinged part: Sheet steel, 1.5 mm<br>Viewing window: Single-pane safety glass, 3 mm  |
| Surface finish  | Powder-coated  |
| Colour          | Wall and hinged part: RAL 7035<br>Glazed door: RAL 7035/7015 (slate grey)  |
| Supply includes | Wall section: Gland plate, solid, top and bottom<br>Hinged part with 25 mm pitch pattern of holes in the front and rear frame, and two 482.6 mm (19") mounting angles, front, static installation<br>Designer glazed door<br>Centre part lock: 3 mm double-bit<br>Designer glazed door lock: Security lock 3524 E<br>Comfort handle for lock inserts and 2-point locking |
| Units           | 21 U   |

# Features

|  |  |
|--|--|
| Dimensions                             | Width: 600 mm<br>Height: 1,012 mm<br>Depth: 473 mm   |
| Number of locks                        | 1  |
| Load capacity of hinged part (static)  | 750 N  |
| Load capacity of wall section (static) | 250 N  |
| Basic material                         | Sheet steel  |
| Lock                                   | Lock version: Comfort handle and 2-point locking<br>Lock insert: Security lock insert no. 3524 E               |
| Protection category to IEC 60 529      | IP 54 in conjunction with solid gland plate top and bottom   |
| Packs of                               | 1 pc(s).   |
| Net weight                             | 46.55  |
| Gross weight                           | 49   |
| Note on PCF category                   | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number                  | 94032080   |
| EAN                                    | 4028177983311  |
| ETIM 9                                 | EC002500   |
| ETIM 8                                 | EC002500   |
| ECLASS 8.0                             | 27180101   |

# Approvals

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|

# Tender text

AX wall-mounted enclosure 3-part, 21 U, depth 473 mm

Enclosure: 3-part wall-mounted enclosure consisting of:

Wall section with solid gland plate at the top and bottom, may optionally be exchanged for cable entry variants (accessories), holes for wall-mounting,

Hinged section with 2 pcs. 482,6 mm (19")

mounting angles fitted at the front with all-around 25 mm pitch pattern in the front and rear frame.

Designer glazed door with comfort handle for lock inserts, with security lock 3524 E, may optionally be exchanged for comfort handle for semi cylinder (accessory)

Material enclosure: sheet steel 1,5 mm,

Material glazed door: single-pane safety glass, 3 mm

Surface finish: powder-coated

Color wall and hinged part: RAL 7035

Color glazed door: RAL 7035/7015 (slate grey)

Protection category: IP 55 nach EN 60 529

Dimension (W x H x D): 600 x 1012 x 473 mm, 21 U

Manufacturer: Rittal GmbH & Co. KG