

# Rittal – The System.

Faster – better – everywhere.



## SR 2340.700

# Nihajni okvir, velik, brez obrobe

State: 22.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SR 2340.700 - Nihajni okvir, velik, brez obrobe za ohišja TS, VX SE, širine 600 mm in 1200 mm

Za ohišja širine 600 mm in 1200 mm, 22–45 U, brez okrasne plošče, za namestitvev 482,6 mm (19") opreme.



## Features

Št. Modela	SR 2340.700
Opis izdelka	Za montažo 482,6 mm (19") komponent.
Material	Jeklena pločevina
Površinska obdelava	Pocinkano
Obseg dobave	Odmična ključavnica z dvojnimi vložki Deli za pritrditev na montažni komplet
Navodila za sestavljanje	Glede na montažno situacijo so potrebni TS luknjani profili z montažnimi prirobnicami 23 x 73 mm ali 17 x 73 mm
Opomba	Za dodatne možnosti namestitve glejte "Tehnične podrobnosti"
Primerno za	Vrsta ohišja: TS Širina: = 600 mm = 1.200 mm Višina: ≥ 2.000 mm
Enote	40 U
Za tip ohišja	TS
Paketi	1 pc(s).
Neto teža	12,271 kg

# Features

Bruto teža	12,917 kg
Carinska tarifna številka	94039910
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Opis izdelka	SR Swing frame, large without trim panel, for TS, VX SE, for W: 600/1200 mm, 40 U