


# Rittal – The System.

Faster – better – everywhere.



## SG 2370.161

# LED komponenta za stalno svetlobo

State: 23.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2370.161 - LED komponenta za stalno svetlobo za signalni steber, modularno

S 360° oddajanjem signala zahvaljujoč optimizirani tehnologiji prizme.

## Features

Št. Modela	SG 2370.161
Zasnova	LED komponenta za stalno svetlobo
Prednosti	S 360° prenosom signala z optimiziranim sistemom prizem Konfiguracija do petih komponent z enako napetostjo.
Način delovanja	Možna je modularna zasnova s priključki, optičnimi in akustičnimi komponentami ter označevalno ploščo
Material	Ohišje iz poliamida Pokrovček: prozoren polikarbonat
Barva	Zelena
Razred zaščite po IEC 60 529	IP 65 if a cover or acoustic component is fitted at the top
Nazivna delovna napetost	230 V
Paketi	1 pc(s).
Neto teža	0,071 kg
Bruto teža	0,073 kg
Carinska tarifna številka	85311095
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220
Opis izdelka	SG LED steady light component, green

## Approvals

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

---